



Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, .50-.61" Cable Range

By Bryant
Catalog # PA050



Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, .50-.61" Cable Range

Application

General Cable Pulling

General

Approx Breaking Strength	2,800 lbs
Catalog Number	PA050
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	560
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Light Duty Grip

Style	Closed Mesh, Single Weave
Type	Flexible Eye
UPC	781786280441

Conductor Related

Cable Diameter Range	0.50 in-0.61 in
Cable Size	.50-.61" (1.27-1.55)
Cable Specification	UL Listed Circuit Wire

Product Assets

- [Catalog Page - BRY N-6 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - PA050](#)