



# Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.25-1.49" Cable Range

By Bryant  
Catalog # [PA125](#)

Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.25-1.49" Cable Range



## Application

General Cable Pulling

## General

Approx Breaking Strength	5,300 lbs
Construction	Woven
Load Capacity	1060
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Light Duty Grip
Style	Closed Mesh, Single Weave
Type	Flexible Eye
UPC	781786280526

## Conductor Related

Cable Diameter Range	1.25 in-1.49 in
Cable Size	1.25-1.49" (3.17-3.78)
Cable Specification	UL Listed Circuit Wire

## Product Assets

[Catalog Page - Bryant N-6 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Wiring\\_WLFVM032](#)  
[Literature - Wiring\\_WLBVM044](#)  
[Literature - Pulp & Paper Solutions](#)

## Related Products

[PJ075 - Bryant Wire and Cable Management, Junior Low Tension Pulling Grip, Flexible Eye, .75-.99" Cable Range](#)  
[PA175 - Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.75-1.99" Cable Range](#)  
[PA300 - Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 3.00-3.49" Cable Range](#)  
[PJ050 - Bryant Wire and Cable Management, Junior Low Tension Pulling Grip, Flexible Eye, .50-.61" Cable Range](#)  
[PA100 - Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.00-1.24" Cable Range](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-PA125-SPEC-EN | REV 7/2023