



# Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 2.00-2.49" Cable Range

By Bryant  
Catalog # [PA200](#)

Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 2.00-2.49" Cable Range



## Application

General Cable Pulling

## General

Approx Breaking Strength	8,500 lbs
Construction	Woven
Load Capacity	1700
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Light Duty Grip
Style	Closed Mesh, Single Weave
Type	Flexible Eye
UPC	781786280588

## Conductor Related

Cable Diameter Range	2.00 in-2.49 in
Cable Size	2.00-2.49" (5.08-6.32)
Cable Specification	UL Listed Circuit Wire

## Product Assets

[Catalog Page - Bryant N-6 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[PA125 - Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.25-1.49" Cable Range](#)  
[PA075 - Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, .75-.99" Cable Range](#)  
[PA150 - Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.50-1.74" Cable Range](#)  
[PJ062 - Bryant Wire and Cable Management, Junior Low Tension Pulling Grip, Flexible Eye, .62-.74" Cable Range](#)  
[PJ025 - Bryant Wire and Cable Management, Junior Low Tension Pulling Grip, Flexible Eye, .25-.36" Cable Range](#)



A proud member of the Hubbell Family.