



Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240V, Terminal Screws

By Bryant
Catalog # [PCS002](#)

Switches and Lighting Controls, Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240V, Terminal Screws, Yellow



General

Actuator	Push Buttons
Color	Yellow
Contact Configuration	Momentary
Enclosure Type	NEMA 4X
Environmental Conditions	Indoor and Outdoor
Indicator(s) Type	None
Item Type	Complete Unit- 2 Buttons
Material	Non-Metallic
Material - Mounting Hardware	Cable Mounted
OEM Brand Name	Hubbell Bryant
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Compact
Style	Two Button
Type	Single Speed
UPC	781786406407

Dimensions

Display Size	Compact
--------------	---------

Electrical Ratings

Connectivity	Terminal Screws
Contact Rating	Pilot Duty Only
Current Rating	6 A
Phase	Single Phase
Voltage Rating	250V AC Max kV

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant G-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[PCS202 - Industrial Grade, Pendant Controls, Two Button Compact Version, Two Speed Normally Open, Pilot Duty, 240V, Terminal Screws](#)
[PCS102 - Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240V, Terminal Screws](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-PCS002-SPEC-EN | REV 7/2023