



Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240V, Terminal Screws

By Bryant
Catalog # [PCS102](#)



Switches and Lighting Controls, Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240V ,Terminal Screws, Yellow

General

Actuator	Push Buttons
Back Box Type	-
Color	Yellow
Contact Configuration	Momentary
Enclosure Type	NEMA 4X
Environmental Conditions	Indoor and Outdoor
Indicator(s) Type	None
Item Type	Complete Unit- 2 Buttons
Material	Non-Metallic
Material - Mounting Hardware	Cable Mounted
OEM Brand Name	Hubbell Bryant
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Compact
Style	Two Button
Type	Single Speed
UPC	781786406421

Dimensions

Display Size	Compact
--------------	---------

Electrical Ratings

Connectivity	Terminal Screws
Contact Rating	Pilot Duty Only
Current Rating	6 A
Phase	Single Phase
Voltage Rating	250V AC Max kV

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant G-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[PCS002 - Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240V, Terminal Screws](#)
[PCS202 - Industrial Grade, Pendant Controls, Two Button Compact Version, Two Speed Normally Open, Pilot Duty, 240V, Terminal Screws](#)



A proud member of the Hubbell Family.