



Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, 1.00-1.49" Cable Range

By Bryant
Catalog # [PH100](#)

Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, 1.00-1.49" Cable Range



Application

General Cable Pulling

General

Approx Breaking Strength	9,600 lbs
Construction	Woven
Load Capacity	1920
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Underground T-Type
Style	Closed Mesh, Double Weave
Type	Flexible Eye, Short Length
UPC	781786280328

Conductor Related

Cable Diameter Range	1.00 in-1.49 in
Cable Size	1.00-1.49" (2.54-3.78)
Cable Specification	UL Listed Circuit Wire

Product Assets

[Catalog Page - Bryant N-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Wiring_WLFVM032](#)
[Literature - Wiring_WLBVM044](#)
[Literature - Pulp & Paper Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-PH100-SPEC-EN | REV 7/2023