



Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, 3.50-3.99" Cable Range

By Bryant
Catalog # [PH350](#)

Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, 3.50-3.99" Cable Range



Application

General Cable Pulling

General

Approx Breaking Strength	31,000 lbs
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	6200
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Underground T-Type
Style	Closed Mesh, Double Weave
Type	Flexible Eye, Short Length
UPC	781786280427

Conductor Related

Cable Diameter Range	3.50 in-3.99 in
Cable Size	3.50-3.99" (8.89-10.13)
Cable Specification	UL Listed Circuit Wire

Product Assets

[Catalog Page - BRY N-5 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Wiring_WLFVM032](#)
[Literature - Wiring_WLBVM044](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRY-PH350-SPEC-EN | REV 5/2024