



Bryant Wire and Cable Management, Pulling Grip, Underground Revolving Eye, .50-.61" Cable Range

By Bryant
Catalog # [PHS050](#)

Bryant Wire and Cable Management, Pulling Grip, Underground Revolving Eye, .50-.61" Cable Range



Application

General Cable Pulling

General

Approx Breaking Strength	4,800 lbs
Construction	Woven
Load Capacity	960
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Underground K-Type
Style	Closed Mesh, Double Weave
Type	Revolving Eye, Short Length
UPC	781786280007

Conductor Related

Cable Diameter Range	0.50 in-0.61 in
Cable Size	.50-.61" (1.27-1.55)
Cable Specification	UL Listed Circuit Wire

Product Assets

[Catalog Page - Bryant N-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Wiring_WLFVM032](#)
[Literature - Wiring_WLBVM044](#)
[Literature - Pulp & Paper Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-PHS050-SPEC-EN | REV 7/2023