



Bryant Wire and Cable Management, Pulling Grip, Underground Revolving Eye, .62-.74" Cable Range

By Bryant
Catalog # [PHS062](#)

Bryant Wire and Cable Management, Pulling Grip, Underground Revolving Eye, .62-.74" Cable Range



Application

General Cable Pulling

General

Approx Breaking Strength	6,800 lbs
Construction	Woven
Load Capacity	1360
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Underground K-Type
Style	Closed Mesh, Double Weave
Type	Revolving Eye, Short Length
UPC	781786280021

Conductor Related

Cable Diameter Range	0.62 in-0.74 in
Cable Size	.62-.74" (1.57-1.88)
Cable Specification	UL Listed Circuit Wire

Product Assets

[Catalog Page - Bryant N-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Wiring_WLFVM032](#)
[Literature - Wiring_WLBVM044](#)
[Literature - Pulp & Paper Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-PHS062-SPEC-EN | REV 7/2023