



Bryant Wire and Cable Management, Pulling Grip, Underground Revolving Eye, .75-.99" Cable Range

By Bryant
Catalog # [PHS075](#)

Bryant Wire and Cable Management, Pulling Grip, Underground Revolving Eye, .75-.99" Cable Range



Application

General Cable Pulling

General

Approx Breaking Strength	9,600 lbs
Construction	Woven
Load Capacity	1920
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Underground K-Type
Style	Closed Mesh, Double Weave
Type	Revolving Eye, Standard Length
UPC	781786280045

Conductor Related

Cable Diameter Range	0.75 in-0.99 in
Cable Size	.75-.99" (1.90-2.51)
Cable Specification	UL Listed Circuit Wire

Product Assets

- [Catalog Page - Bryant N-5 Catalog page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Wiring_WLFVM032](#)
- [Literature - Wiring_WLBVM044](#)
- [Literature - Pulp & Paper Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-PHS075-SPEC-EN | REV 7/2023