



Switches and Lighting Controls, Dimmers, Replacement Rotary Knob, Ivory

By Bryant
Catalog # [R28032406](#)

Switches and Lighting Controls, Dimmers, Replacement Rotary
Knob, Ivory



General

Color	<ul style="list-style-type: none">IvoryIvoire
Construction	Polycarbonate
Environmental Conditions	Indoor Use Only
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Replacement Knobs
UPC	883778117107

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog Page - Bryant F-15 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RFSQ2FDK - Switches and Lighting Control, Residential Grade, Motor Speed Control, Pre-Set Rotary Type, Single Pole, 15A 120V AC, Ivory/White](#)
[R28032401 - Switches and Lighting Controls, Dimmers, Replacement Rotary Knob, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-R28032406-SPEC-EN | REV 7/2023