



Switches and Lighting Controls, Dimmer, Toggle, Single Pole, 600W 120V AC, Light Almond

By Bryant
Catalog # [RAY600PLA](#)

Switches and Lighting Controls, Dimmer, Toggle, Single Pole,
600W 120V AC, Light Almond



Features

- No Neutral Required
- Low End Adjustment for Fine Tuning
- Traditional Toggle Styling Available

General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Color	<ul style="list-style-type: none">• Light Almond• Amande Clair
Construction	Metal Strap, Polycarbonate Front
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Toggle Dimmer
Type	<ul style="list-style-type: none">• Incandescent• Incandescent
UPC	883778116834

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	5 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	600 W

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

Related Products

- [RAYCL153PW - Switches and Lighting Controls, Dimmer for Compact Fluorescent and LED, Single Pole and Three Way, White](#)
- [RAYCL153PLA - Switches and Lighting Controls, Dimmer, Rotary, Three Way, CFL and LED Loads, Light Almond](#)
- [RDVCL153PI - Switches and Lighting Controls, Dimmer, Rotary, Single Pole and Three Way, CFL and LED Loads, Ivory](#)
- [RDVCL153PLA - Switches and Lighting Controls, Dimmer, Rotary, Single Pole and Three Way, CFL and LED Loads, Light Almond](#)
- [RAYCL153PI - Switches and Lighting Controls, Dimmer for Compact Fluorescent and LED, Single Pole and Three Way, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RAY600PLA-SPEC-EN | REV 7/2023