



Switches and Lighting Controls, Dimmer, Toggle, Three Way, 600W 120V AC, Light Almond

By Bryant
Catalog # [RAY603PLA](#)

Switches and Lighting Controls, Dimmer, Toggle, Three Way,
600W 120V AC, Light Almond



General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Catalog Number	RAY603PLA
Color	Light Almond
Construction	Metal Strap, Polycarbonate Front
EU RoHS Indicator	No
Environmental Conditions	Indoor Use Only
Number Of Poles	3-Way
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Specifications	<ul style="list-style-type: none">Product Type - Toggle Preset DimmersTermination - Three Way
Style	Toggle Dimmer
Type	Incandescent
UPC	883778116872

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	5 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	600 W

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Specifications - RAY603PLA](#)



A Hubbell brand