



# Switches and Lighting Controls, Dimmer for Compact Fluorescent and LED, Single Pole and Three Way, Ivory

By Bryant  
Catalog # RAYCL153PI



Switches and Lighting Controls, Dimmer for Compact  
Fluorescent and LED, Single Pole and Three Way, Ivory

## Features

- Optimum CFL and LED Control
- Low End Adjustment for Fine Tuning
- Decorator and Traditional Toggle Styling Available

## General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Catalog Number	RAYCL153PI
Color	<ul style="list-style-type: none"><li>• Ivory</li><li>•</li></ul>
Construction	Metal Strap, Polycarbonate Front
EU RoHS Indicator	No
Environmental Conditions	Indoor Use Only
Material - Mounting Hardware	Screws and Wire connectors included
Number Of Poles	Single Pole / 3-Way
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Toggle Dimmer
Type	<ul style="list-style-type: none"><li>• LED/CFL</li><li>• LED/CFL</li></ul>
UPC	883778304552

## Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

## Electrical Ratings

Amperage Rating	1.25 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	150 W

## Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	6
-----------------	---

## Product Assets

[Catalog Page - BRY F-14 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)