



Switches and Lighting Controls, Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Pilot Light, 15A 120V AC, Self Grounding, Side Wired

By Bryant
Catalog # RC109LA



One Single-Pole Toggle One Pilot Light Combination Device,
Residential 15A 120V AC, Self Grounding, Side Wired

General

Action	Snap Switch
Actuator	Toggle
Application	Residential
Catalog Number	RC109LA
Color	
Contact Configuration	Two Position
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Switch and Amber Pilot Light Combo Device
Material - Mounting Hardware	Mounting Screws
Number Of Poles	1) Single Pole
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
Performance	Environmental - Operating temperature - -20°C to 60°C
UPC	883778119095

Dimensions

Display Size	Standard Size
--------------	---------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC
Wattage	1800

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK Z-15 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-RC109LA-SPEC-EN | REV 6/2024