



Switches and Lighting Controls, Combination Devices, Residential Grade, 2) Three Way Toggles, 15A 120V AC, Self Grounding, Side Wired, Almond

By Bryant
Catalog # [RC303AL](#)



Switches and Lighting Controls, Combination Devices, Residential Grade, 2) Three Way Toggles, 15A 120V AC, Self Grounding, Side Wired, Almond

Features

- Quiet snap action mechanism
- Self-grounding staple is standard
- Elongated strap with continuous plaster ears

Application

Residential

General

Action	Snap Switch
Actuator	Toggle
Catalog Number	RC303AL
Contact Configuration	Two Position
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Switch Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	2) Three Way
Operating Cycles	30,000 Minimum

Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
UPC	883778109980

Dimensions

Display Size	Standard Size
--------------	---------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Wattage	1800

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Specifications - RC303AL](#)