BRYANT®

Combination Devices, Residential Grade, 1) Three Way Toggle, 1) **Single Tamper Resistant** Receptacle, 15A 12OV AC , Self Grounding, Side Wired

By Bryant Catalog # RC308ALTR

Switches and Lighting Controls, Combination Devices, Residential Grade, 1) Three Way Toggle, 1) Single Tamper Resistant Receptacle, 15A 120V AC , Self Grounding, Side Wired

Application

Residential

General

Action Actuator Contact Configuration **Environmental Conditions**

Item Type

Material - Mounting Hardware Number Of Poles **Operating Cycles Operating Temperature**

UPC

Snap Switch Toggle Two Position Indoor Dry Unless Protected By Additional Means Traditional Switch and **Receptacle Combo Devices** Mounting Screws 1) Three Way 30,000 Minimum Max Continuous- 60 Degrees C, Minimum- -20 Without Impact 883778302282



Standard Size

Dimensions

Display Size **Electrical Ratings** Amperage Rating 15 A Connectivity Side Wired Contact Rating 15A 15 A Current / Amperage Rating **Current Rating** 15 A Voltage Rating 120 VAC 1800 Wattage Logistics Carton Quantity 10

Product Assets

