



Combination Devices, Residential Grade, Decorator Series, 1) Single Pole Rocker, 1) Tamper Resistant Single Receptacle, 15A 120V AC, Side Wired

By Bryant
Catalog # [RCD108LATR](#)



Switches and Lighting Controls, Combination Devices, Residential Grade, Decorator Series, 1) Single Pole Rocker, 1) Tamper Resistant Single Receptacle, 15A 120V AC, Side Wired

Features

- Smooth, quiet rocker
- Low profile, less than 1 inch deep
- Self-grounding feature is standard

Application

Residential

General

Action	Snap Switch
Actuator	Rocker
Contact Configuration	Two Position
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Switch and Receptacle Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	1) Single Pole
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
Performance	<ul style="list-style-type: none">• Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute• Electrical - Endurance - 30,000 cycles minimum• Electrical - Max. working voltage - 120V• Electrical - Overload - 1.5 times rating• Environmental - Flammability - UL V0• Environmental - Operating temperatures - Maximum continuous 60°C• minimum -20°C (without impact)• Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only

Dimensions

Display Size Standard Size

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed E3896
----------------------	---

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant E-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)
[Literature - Residential Catalog](#)

Related Products

[RCD108GYTR - Combination Devices, Residential Grade, Decorator Series, 1\) Single Pole Rocker, 1\) Tamper Resistant Single Receptacle, 15A 120V AC, Side Wired](#)

[RCD101LA - Switches and Lighting Controls, Combination Devices, Residential Grade, Decorator Series, 2\) Single Pole Rockers, 15A 120V AC, Side Wired](#)

[RCD111LA - Switches and Lighting Controls, Combination Devices, Residential Grade, Decorator Series, 3\) Three Way Rockers, 15A 120V AC, Side Wired, Light Almond](#)

[RCD108WTR - Combination Devices, Residential Grade, Decorator Series, 1\) Single Pole Rocker, 1\) Single Tamper Resistant Receptacle, 15A 120V AC, Side Wired](#)

[RCD108BKTR - Combination Devices, Residential Grade, Decorator Series, 1\) Single Pole Rocker, 1\) Tamper Resistant Single Receptacle, 15A 120V AC, Side Wired](#)

- push wire: #14 AWG solid copper wire only

UPC

883778302374



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RCD108LATR-SPEC-EN | REV 7/2023