



# Combination Devices, Residential Grade, Decorator Series, 1) Three Way Pole Rocker, 1) Tamper Resistant Single Receptacle, 15A 120V AC

By Bryant  
Catalog # [RCD308WTR](#)



Switches and Lighting Controls, Combination Devices, Residential Grade, Decorator Series, 1) Three Way Pole Rocker, 1) Tamper Resistant Single Receptacle, 15A 120V AC, Side

## Features

- Smooth, quiet rocker
- Low profile, less than 1 inch deep
- Self-grounding feature is standard

## Application

Residential

## General

Action	Snap Switch
Actuator	Rocker
Contact Configuration	Two Position
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Switch and Receptacle Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	1) Three Way
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
Performance	<ul style="list-style-type: none"><li>• Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute</li><li>• Electrical - Endurance - 30,000 cycles minimum</li><li>• Electrical - Max. working voltage - 120V</li><li>• Electrical - Overload - 1.5 times rating</li><li>• Environmental - Flammability - UL V0</li><li>• Environmental - Operating temperatures - Maximum continuous 60°C</li><li>• minimum -20°C (without impact)</li><li>• Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only</li></ul>

## Dimensions

Display Size                      Standard Size

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• UL Listed E3896</li></ul>
----------------------	---

## Logistics

Carton Quantity                      10

## Product Assets

[Catalog Page - Bryant E-7 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)  
[Literature - Residential Catalog](#)

## Related Products

[RCD308LATR - Combination Devices, Residential Grade, Decorator Series, 1\) Three Way Pole Rocker, 1\) Tamper Resistant Single Receptacle, 15A 120V AC](#)  
[RCD109W - Combination Devices, Residential Grade, Decorator Series, 1\) Single Pole Rocker, 1\) Pilot Light, 15A 120V AC, Side Wired](#)  
[RCD101W - Switches and Lighting Controls, Combination Devices, Residential Grade, Decorator Series, 2\) Single Pole Rockers, 15A 120V AC, Side Wired, White](#)  
[RCD309W - Switches and Lighting Controls, Combination Devices, Residential Grade, 1\) Three Way Switch 1\) Pilot Light Clear, 15A 120V, White](#)  
[RCD108WTR - Combination Devices, Residential Grade, Decorator Series, 1\) Single Pole Rocker, 1\) Single Tamper Resistant Receptacle, 15A 120V AC, Side Wired](#)

- push wire: #14 AWG solid copper wire only

UPC

883778302442



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RCD308WTR-SPEC-EN | REV 7/2023