



Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, Ivory or White

By Bryant
Catalog # [RD600PDK](#)

Switches and Lighting Controls, Dimmer, Rotary, Single Pole,
600W 120V AC, Ivory or White



Features

- No Neutral Required
- Low End Adjustment for Fine Tuning

General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Color	<ul style="list-style-type: none">• Ivory and White• Ivoire et blanc
Construction	Metal Strap, Polycarbonate Front
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Rotary Dimmer
Type	<ul style="list-style-type: none">• Incandescent• Incandescent
UPC	883778117060

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	5 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	600 W

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog Page - Bryant F-15 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RD600RW - Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, White](#)
[RRKDK - TradeSelect, Replacement Rotary Knobs, White and Ivory](#)
[RS603PW - TradeSelect, Switches and Lighting Controls, Dimmers, Pre-Set Slider, Three Way, 600W 120V AC, White](#)
[RD603PDK - Switches and Lighting Controls, Dimmer, Rotary, Three Way, 600W 120V AC, Ivory/White](#)
[RS603PI - TradeSelect, Switches and Lighting Controls, Dimmers, Pre-Set Slider, Three Way, 600W 120V AC, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RD600PDK-SPEC-EN | REV 7/2023