



Switches and Lighting Controls, Dimmer Switch, Illuminated Rocker, Single Pole, 1000 Watts 120V AC, Ivory

By Bryant
Catalog # [RDV10PI](#)

Switches and Lighting Controls, Dimmer Switch, Illuminated
Rocker, Single Pole, 1000 Watts 120V AC, Ivory



General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Color	<ul style="list-style-type: none">IvoryIvoire
Construction	Metal Strap, Polycarbonate Front
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Rocker Dimmer
Type	Incandescent
UPC	883778116100

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	8 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	1000 W

Certifications and Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	6
-----------------	---

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RDV10PI-SPEC-EN | REV 7/2023