



# Switches and Lighting Controls, Dimmer, Rocke, Illuminated, SinglePole, 1000W 120V AC, White

By Bryant  
Catalog # [RDV10PW](#)

Switches and Lighting Controls, Dimmer, Rocke, Illuminated,  
SinglePole, 1000W 120V AC, White



## General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Color	<ul style="list-style-type: none"><li>White</li><li>Blanc</li></ul>
Construction	Metal Strap, Polycarbonate Front
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Rocker Dimmer
Type	Incandescent
UPC	883778116094

## Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

## Electrical Ratings

Amperage Rating	8 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	1000 W

## Certifications and Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

## Logistics

Carton Quantity	6
-----------------	---

## Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RDV10PW-SPEC-EN | REV 7/2023