



Switches and Lighting Controls, Dimmer, Rotary, Single Pole and Three Way, CFL and LED Loads, Light Almond

By Bryant
Catalog # [RDVCL153PLA](#)



Switches and Lighting Controls, Dimmer, Rotary, Single Pole and Three Way, CFL and LED Loads, Light Almond

Features

- Optimum CFL and LED Control
- Low End Adjustment for Fine Tuning
- Decorator and Traditional Toggle Styling Available

General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Color	<ul style="list-style-type: none"> • Light Almond • Amande Clair
Construction	Metal Strap, Polycarbonate Front
Environmental Conditions	Indoor Use Only
Material - Mounting Hardware	Screws and Wire connectors included
Number Of Poles	Single Pole / 3-Way
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Rocker Dimmer
Type	<ul style="list-style-type: none"> • LED/CFL • LED/CFL
UPC	883778304538

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	1.25 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	150 W

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog Page - Bryant F-14 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RAYCL153PLA - Switches and Lighting Controls, Dimmer, Rotary, Three Way, CFL and LED Loads, Light Almond](#)
[RDVCL153PW - Switches and Lighting Controls, Dimmer, Rotary, Single Pole and Three Way, CFL and LED Loads, White](#)
[RAYCL153PW - Switches and Lighting Controls, Dimmer for Compact Fluorescent and LED, Single Pole and Three Way, White](#)
[RDVCL153PI - Switches and Lighting Controls, Dimmer, Rotary, Single Pole and Three Way, CFL and LED Loads, Ivory](#)
[RAYCL153PI - Switches and Lighting Controls, Dimmer for Compact Fluorescent and LED, Single Pole and Three Way, Ivory](#)



A proud member of the Hubbell Family.