



Switches and Lighting Controls, Speed Control, Rocker, 1.5A 120V AC, Ivory

By Bryant
Catalog # [RDVFSQFI](#)

Switches and Lighting Controls, Speed Control, Rocker, 1.5A
120V AC, Ivory



General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Color	<ul style="list-style-type: none">IvoryIvoire
Construction	Metal Strap, Polycarbonate Front
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Rocker Fan Control
Type	Fan Control
UPC	883778116179

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	1.5 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	180 W

Certifications and Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog Page - Bryant F-15 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Residential Catalog](#)

Related Products

[RAYFSQFW - Switches and Lighting Control, Residential Grade, Motor Speed Control, Toggle Type, Single Pole, 15A 120V AC, White](#)
[RSFSQFW - TradeSelect, Switches and Lighting Control, Residential Grade, Motor Speed Control, Slider Type, Single Pole, 1.5A 120V AC, White](#)
[RAYFSQFI - Switches and Lighting Control, Residential Grade, Motor Speed Control, Toggle Type, Single Pole, 15A 120V AC, Ivory](#)
[RDVFSQFLA - Switches and Lighting Controls, Speed Control, Rocker, 1.5A 120V AC, Light Almond](#)
[RSFSQFLA - TradeSelect, Switches and Lighting Control, Speed Control, Slider, Single Pole, 1.5A 120V AC, Light Almond](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RDVFSQFI-SPEC-EN | REV 7/2023