



Net Select, JLOAD Box, Deep, Non-Metallic Clamps

By Bryant
Catalog # [RJ600](#)

NetSELECT, JLOAD Box, Deep, Non-Metallic Clamps



Application

Ideal for flat panels TVs

General

Color	<ul style="list-style-type: none">• Metallic• Métallique
Contact	Steel
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Box Only
Material - Mounting Hardware	Screw Mounting
UPC	883778113031

Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant P-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [RJ620BKTR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Black](#)
- [RJ620LATR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Light Almond](#)
- [RU100W - Under Cabinet Distribution Box, Slim, Metallic, White](#)
- [RJ650WTR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, White](#)
- [RJ620ITR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RJ600-SPEC-EN | REV 7/2023