



# J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Black

By Bryant  
Catalog # [RJ620GYTR](#)

J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle,  
Cat 6 Jack, F Coax, Decorator Frame, Black



## Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

## Application

Ideal for flat panels TVs

## General

Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gris</li> </ul>
Contact	Beryllium Copper, Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Complete Unit
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302596

## Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

## Electrical Ratings

Connectivity	Terminal Screws for Receptacle
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

## Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant P-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [RJ620BKTR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Black](#)
- [RU100SS - Under Cabinet Distribution Box, Slim, Metallic, Stainless Steel](#)
- [RJ62GYTR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Gray](#)
- [RJ620WTR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, White](#)
- [RU170W - Under Cabinet Distribution Box, Slim, Non-Metallic, Stainless Steel](#)



A proud member of the Hubbell Family.