



J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Ivory

By Bryant
Catalog # RJ620ITR



J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle,
Cat 6 Jack, F Coax, Decorator Frame, Ivory

General

Application	Ideal for flat panels TVs
Catalog Number	RJ620ITR
Color	Ivory
Contact	Beryllium Copper, Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Complete Unit
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302602

Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

Electrical Ratings

Connectivity	Terminal Screws for Receptacle
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Brochures - Floorbox Selection Guide](#)
- [Catalog Page - WDK Z-18 Catalog Page](#)
- [Catalog Page - WDK Z-27 Catalog Page](#)
- [Catalog Page - WDK Z-21 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand