



J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2- Port, Decorator Frame, Almond

By Bryant
Catalog # [RJ62ALTR](#)

J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle,
2-Port, Decorator Frame, Almond



Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

Application

Ideal for flat panels TVs

General

Color	<ul style="list-style-type: none">• Almond• Amande
Contact	Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Frame and Receptacle Only
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302633

Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

Electrical Ratings

Connectivity	Terminal Screws for Receptacle
--------------	-----------------------------------

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

Related Products

- [RJ62GYTR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Gray](#)
- [RJ62WTR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, White](#)
- [RJ62ITR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Ivory](#)
- [RJ650ITR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Ivory](#)
- [RJ600 - Net Select, JLOAD Box, Deep, Non-Metallic Clamps](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RJ62ALTR-SPEC-EN | REV 7/2023