



# J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2- Port, Decorator Frame, Light Almond

By Bryant  
Catalog # [RJ62LATR](#)

J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle,  
2-Port, Decorator Frame, Light Almond



## Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

## Application

Ideal for flat panels TVs

## General

Color	<ul style="list-style-type: none"><li>• Light Almond</li><li>• Amande Clair</li></ul>
Contact	Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Frame and Receptacle Only
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302671

## Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

## Electrical Ratings

Connectivity	Terminal Screws for Receptacle
--------------	-----------------------------------

## Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant P-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[RU170W - Under Cabinet Distribution Box, Slim, Non-Metallic, Stainless Steel](#)

[RU100SS - Under Cabinet Distribution Box, Slim, Metallic, Stainless Steel](#)

[RJ65LATR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Light Almond](#)

[RJ600 - Net Select, JLOAD Box, Deep, Non-Metallic Clamps](#)

[RJ62WTR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RJ62LATR-SPEC-EN | REV 7/2023