



# J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Light Almond

By Bryant  
Catalog # [RJ650LATR](#)

J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Light Almond



## Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

## Application

Ideal for flat panels TVs

## General

Color	<ul style="list-style-type: none"> <li>• Light Almond</li> <li>• Amande Clair</li> </ul>
Contact	Beryllium Copper, Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Complete Unit
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302497

## Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

## Electrical Ratings

Connectivity	Terminal Screws for Receptacle
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

## Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant P-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[RJ650GYTR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Gray](#)  
[RJ650BKTR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Black](#)  
[RU100W - Under Cabinet Distribution Box, Slim, Metallic, White](#)  
[RJ62LATR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Light Almond](#)  
[RU170W - Under Cabinet Distribution Box, Slim, Non-Metallic, Stainless Steel](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RJ650LATR-SPEC-EN | REV 7/2023