



J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Ivory

By Bryant
Catalog # [RJ65ITR](#)

J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Ivory



Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

Application

Ideal for flat panels TVs

General

Color	<ul style="list-style-type: none"> • Ivory • Ivoire
Contact	Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Frame and Receptacle Only
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302541

Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

Electrical Ratings

Connectivity	Terminal Screws for Receptacle
--------------	--------------------------------

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant P-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [RJ65GYTR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Gray](#)
- [RU170W - Under Cabinet Distribution Box, Slim, Non-Metallic, Stainless Steel](#)
- [RJ62ITR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Ivory](#)
- [RJ600 - Net Select, JLOAD Box, Deep, Non-Metallic Clamps](#)
- [RJ650ITR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RJ65ITR-SPEC-EN | REV 7/2023