



J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, White

By Bryant
Catalog # [RJ65WTR](#)

J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, White



Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

Application

Ideal for flat panels TVs

General

Color	<ul style="list-style-type: none"> • White • White
Contact	Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Frame and Receptacle Only
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302565

Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

Electrical Ratings

Connectivity	Terminal Screws for Receptacle
--------------	--------------------------------

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant P-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [RU100SS - Under Cabinet Distribution Box, Slim, Metallic, Stainless Steel](#)
- [RJ600 - Net Select, JLOAD Box, Deep, Non-Metallic Clamps](#)
- [RJ65GYTR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Gray](#)
- [RU170W - Under Cabinet Distribution Box, Slim, Non-Metallic, Stainless Steel](#)
- [RJ65LATR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Light Almond](#)



A proud member of the Hubbell Family.