



Lamp Holders and Sockets, Medium Base, Turn Knob, 660W 600V AC, Brass

By Bryant
Catalog # [RL101](#)

Lamp Holders and Sockets, Medium Base, Turn Knob, 660W
600V AC, Brass



Application

Brass Lampholders, Medium Base

General

Color	<ul style="list-style-type: none">• Brass• Laiton
Item Type	Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Series	Lampholders
Type	Incandescent, Brass
UPC	883778112119

Electrical Ratings

Amperage Rating	1 A
Connectivity	Screw Terminals
Current / Amperage Rating	1 A
Current Rating	1 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

Certifications and Compliance

Industry Standard(s) UL or cUL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant O-2 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [RL105 - Incandescent Lamp Sockets, Push, Brass Shell, 600W 600V](#)
- [RL8512 - Lamp Holders and Sockets, Medium Base, Pull Chain, 600W 250V, 2 Terminals, Plastic](#)
- [RL102 - Lamp Holders and Sockets, Medium Base, Turn Knob, 2-Circuit, 660W 600V AC, Brass](#)
- [RL100 - Incandescent Lamp Sockets, Keyless, Brass Shell, 600W 600V](#)
- [RL106 - Incandescent Lamp Sockets, Pull Chain, Brass Shell, 600W 600V](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL101-SPEC-EN | REV 7/2023