



Lamp Holders and Sockets, Medium Base, Pigtail, 660W 250V, Rubber with Leads

By Bryant
Catalog # [RL124](#)



Lamp Holders and Sockets, Medium Base, Pigtail, 660W 250V,
Rubber with Leads

General

Color	<ul style="list-style-type: none">• Black• Noir
Item Type	Replacement Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Material - Mounting Hardware	Pigtail Mount
Series	Lampholder Accessories
Type	Incandescent, Medium Base
UPC	883778112225

Electrical Ratings

Amperage Rating	2.64 A
Connectivity	6" Leads
Current / Amperage Rating	2.64 A
Current Rating	2.64 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

Certifications and Compliance

Industry Standard(s)	cCSAus Certified
----------------------	------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant O-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [RL150 - Lamp Holders and Sockets, Socket Extension, Medium to Medium, Porcelain](#)
- [RL200 - Adapter, Residential Grade, Plug-In, 5- 15R to Medium Base, White](#)
- [RL154 - Lamp Holders and Sockets, Socket Reducer, Mogul to Medium Base, Porcelain](#)
- [RL201 - Adapter, Residential Grade, Plug-In, Medium Base to 5-15R, White](#)
- [RL124H - Lamp Holders and Sockets, Medium Base, 660W 600V AC, Non-Metallic, with Hook](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL124-SPEC-EN | REV 7/2023