



## Lamp Holders and Sockets, Medium Base, 660W 600V AC, Non-Metallic, with Hook

By Bryant  
Catalog # [RL124H](#)



Lamp Holders and Sockets, Medium Base, 660W 600V AC, Non-Metallic, with Hook

### Features

- Medium Base
- 660W 600V AC
- Non-Metallic
- with Hook

### General

Catalog Number	RL124H
Color	Black
EU RoHS Indicator	Yes
Item Type	Replacement Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Material - Mounting Hardware	Socket with Hook
Series	Lampholder Accessories
Type	Incandescent, Medium Base
UPC	883778112249

### Electrical Ratings

Amperage Rating	2.64 A
Connectivity	Insulation Piercing
Current / Amperage Rating	2.64 A
Current Rating	2.64 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

### Certifications And Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog Page - WDK BB-9](#)
- [Catalog Page Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - RL124H](#)