



# Lamp Holders and Sockets, Socket Extension, Medium to Medium, Porcelain

By Bryant  
Catalog # [RL150](#)

Lamp Holders and Sockets, Socket Extension, Medium to Medium, Porcelain



## General

Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
Item Type	Incandescent Adapters
Lamp Size	Medium Base
Material	Composite
Material - Mounting Hardware	Screw-In
Series	Lampholder Accessories
Type	Incandescent, Adaptor, Medium Base
UPC	883778112188

## Electrical Ratings

Amperage Rating	2.64 A
Connectivity	Screw-In
Current / Amperage Rating	2.64 A
Current Rating	2.64 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

## Certifications and Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

### Related Products

- [RL124 - Lamp Holders and Sockets, Medium Base, Pigtail, 660W 250V, Rubber with Leads](#)
- [RL200 - Adapter, Residential Grade, Plug-In, 5- 15R to Medium Base, White](#)
- [RL124H - Lamp Holders and Sockets, Medium Base, 660W 600V AC, Non-Metallic, with Hook](#)
- [RL201 - Adapter, Residential Grade, Plug-In, Medium Base to 5-15R, White](#)
- [RL154 - Lamp Holders and Sockets, Socket Reducer, Mogul to Medium Base, Porcelain](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RL150-SPEC-EN | REV 7/2023