



Incandescent Lamp Sockets, Cleat Socket, Medium Base, 660W 250V, Non Metallic, White

By Bryant
Catalog # [RL153](#)

Incandescent Lamp Sockets, Cleat Socket, Medium Base, 660W 250V, Non Metallic, White



Application

Medium Base Surface and Sign Mount

General

Color	<ul style="list-style-type: none">• Black• Noir
Item Type	Replacement Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Material - Mounting Hardware	2 Piece Surface Mount
Series	Lampholders
Type	Surface & Sign Mount, Medium Base
UPC	883778112218

Electrical Ratings

Amperage Rating	2.64 A
Connectivity	Screw Terminals
Current / Amperage Rating	2.64 A
Current Rating	2.64 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

Certifications and Compliance

Industry Standard(s) C/US UL Listed

Logistics

Carton Quantity 10

Product Assets

Related Products

- [RL163 - Lampholder, Medium Base, Screw Mount, Terminal Screws, 2-Piece, Sign Mount, White](#)
- [RL152 - Lamp Holders and Sockets, Medium Base, Cleat Socket, 660W 250V, Porcelain](#)
- [RL161 - Incandescent Lamp Holders, Medium Base, 2 Piece Surface Mounted](#)
- [RL164 - Incandescent Lamp Holders, Medium Base, 2 Piece Sign Mount, Wire Leads](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL153-SPEC-EN | REV 7/2023