



Incandescent Lamp Holders, Medium Base, Low Profile, Front Mounted Snap-In, Terminal Screws

By Bryant
Catalog # [RL158](#)

Incandescent Lamp Holders, Medium Base, Low Profile, Front Mounted Snap-In, Terminal Screws



Application

Medium Base, Straight Body Keyless Porcelain

General

| | |
|------------------------------|---|
| Color | <ul style="list-style-type: none">• White• Blanc |
| Item Type | Replacement Incandescent Lampholders |
| Lamp Size | Medium Base |
| Material | Composite |
| Material - Mounting Hardware | Front Mount Panel Mount Snap-In |
| Series | Lampholders |
| Type | Straight Body Keyless Porcelain |
| UPC | 883778304101 |

Electrical Ratings

| | |
|---------------------------|-----------------|
| Amperage Rating | 2.64 A |
| Connectivity | Screw Terminals |
| Current / Amperage Rating | 2.64 A |
| Current Rating | 2.64 A |
| Frequency Rating | 60 Hz |
| Voltage Rating | 250V AC kV |

Certifications and Compliance

Industry Standard(s) C/US UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RL159 - Incandescent Lamp Holders, Medium Base, Front Mounted Snap-In, Terminal Screws](#)

[RL162 - Lamp Holders and Sockets, Medium Base, Screw Terminal, Screw Mounted](#)

[RL156 - Lampholder, Medium Base, Screw Mount, 12" Leads, White](#)

[RL157 - Incandescent Lamp Holders, Medium Base, 1/2" Hickey, Terminal Screws](#)

[RL160 - Incandescent Lamp Holders, Medium Base, 1/2" Hickey, 12" Wire Leads](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL158-SPEC-EN | REV 7/2023