



# Incandescent Lamp Holders, Medium Base, 1/2" Hickey, 12" Wire Leads

By Bryant  
Catalog # [RL160](#)



Incandescent Lamp Holders, Medium Base, 1/2" Hickey, 12"  
Wire Leads

## Application

Medium Base, Straight Body Keyless Porcelain

## General

Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
Item Type	Replacement Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Series	Lampholders
Type	Straight Body Keyless Porcelain
UPC	883778304071

## Electrical Ratings

Amperage Rating	2.64 A
Connectivity	12" Leads
Current / Amperage Rating	2.64 A
Current Rating	2.64 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

## Certifications and Compliance

Industry Standard(s) C/US UL Listed

## Logistics

Carton Quantity 10

## Product Assets

## Related Products

[RL159 - Incandescent Lamp Holders, Medium Base, Front Mounted Snap-In, Terminal Screws](#)

[RL158 - Incandescent Lamp Holders, Medium Base, Low Profile, Front Mounted Snap-In, Terminal Screws](#)

[RL156 - Lampholder, Medium Base, Screw Mount, 12" Leads, White](#)

[RL157 - Incandescent Lamp Holders, Medium Base, 1/2" Hickey, Terminal Screws](#)

[RL162 - Lamp Holders and Sockets, Medium Base, Screw Terminal, Screw Mounted](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RL160-SPEC-EN | REV 7/2023