



Lamp Holders and Sockets, Medium Base, Screw Terminal, Screw Mounted

By Bryant
Catalog # RL162



Lamp Holders and Sockets, Medium Base, Screw Terminal, Screw Mounted

Application

Medium Base, Straight Body Keyless Porcelain

General

Color	<ul style="list-style-type: none"> • White • Blanc
Item Type	Replacement Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Material - Mounting Hardware	Screw Mounting
Series	Lampholders
Type	Straight Body Keyless Porcelain
UPC	883778304125

Electrical Ratings

Amperage Rating	2.64 A
Connectivity	Screw Terminals
Current / Amperage Rating	2.64 A
Current Rating	2.64 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

Certifications and Compliance

Industry Standard(s) C/US UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [RL160 - Incandescent Lamp Holders, Medium Base, 1/2" Hickey, 12" Wire Leads](#)
- [RL159 - Incandescent Lamp Holders, Medium Base, Front Mounted Snap-In, Terminal Screws](#)
- [RL157 - Incandescent Lamp Holders, Medium Base, 1/2" Hickey, Terminal Screws](#)
- [RL156 - Lampholder, Medium Base, Screw Mount, 12" Leads, White](#)
- [RL158 - Incandescent Lamp Holders, Medium Base, Low Profile, Front Mounted Snap-In, Terminal Screws](#)



A proud member of the Hubbell Family.