



Adapter, Residential Grade, Plug-In, 5- 15R to Medium Base, White

By Bryant
Catalog # [RL200](#)

Adapter, Residential Grade, Plug-In, 5- 15R to Medium Base, White



General

Color	<ul style="list-style-type: none">• White• Blanc
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Incandescent Adapters
Material	Thermoplastic
Material - Mounting Hardware	Plug-In
Number Of Poles	2-Pole
Series	Lampholder Accessories
Type	Incandescent, Adaptor, Medium Base
UPC	883778112256

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	660

Conductor Related

Number Of Wires	3-Wire Grounding
-----------------	------------------

Certifications and Compliance

Industry Standard(s)	C/US UL Listed
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

Related Products

[RL201 - Adapter, Residential Grade, Plug-In, Medium Base to 5-15R, White](#)

[RL154 - Lamp Holders and Sockets, Socket Reducer, Mogul to Medium Base, Porcelain](#)

[RL150 - Lamp Holders and Sockets, Socket Extension, Medium to Medium, Porcelain](#)

[RL124H - Lamp Holders and Sockets, Medium Base, 660W 600V AC, Non-Metallic, with Hook](#)

[RL124 - Lamp Holders and Sockets, Medium Base, Pigtail, 660W 250V, Rubber with Leads](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL200-SPEC-EN | REV 7/2023