



Adapter, Residential Grade, Plug-In, Medium Base to 5-15R, White

By Bryant
Catalog # [RL201](#)

Adapter, Residential Grade, Plug-In, Medium Base to 5-15R



General

Color	<ul style="list-style-type: none">• White• Blanc
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Incandescent Adapters
Material	Thermoplastic
Material - Mounting Hardware	Plug-In
Number Of Poles	2-Pole
Series	Lampholder Accessories
Type	Incandescent Adaptor, Medium Base
UPC	883778112263

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	660

Conductor Related

Number Of Wires	3-Wire Grounding
-----------------	------------------

Certifications and Compliance

Industry Standard(s)	C/US UL Listed
Nema Rating	5-15P

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant O-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RL202 - Adapter, Residential Grade, Medium Base Current Tap, 2\) Outlet, Pull Chain, 15A 125V, White](#)
[RL124H - Lamp Holders and Sockets, Medium Base, 660W 600V AC, Non-Metallic, with Hook](#)
[RL124 - Lamp Holders and Sockets, Medium Base, Pigtail, 660W 250V, Rubber with Leads](#)
[RL150 - Lamp Holders and Sockets, Socket Extension, Medium to Medium, Porcelain](#)
[RL200 - Adapter, Residential Grade, Plug-In, 5- 15R to Medium Base, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL201-SPEC-EN | REV 7/2023