



# Adapter, Residential Grade, Medium Base Current Tap, 2) Outlet, Pull Chain, 15A 125V, White

By Bryant  
Catalog # [RL202](#)

Adapter, Residential Grade, Medium Base Current Tap, 2)  
Outlet, Pull Chain, 15A 125V, White



## Application

Straight Blade to Straight Blade

## General

Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Replacement Incandescent Lampholders
Material	Thermoplastic
Material - Mounting Hardware	Plug-In
Number Of Poles	2-Pole
Series	Lampholder Accessories
Type	Incandescent, Medium Base
UPC	883778112270

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Phase	Single Phase
Voltage Rating	125V/250V kV
Wattage	Multi

## Conductor Related

Number Of Wires 3-Wire Grounding

## Certifications and Compliance

Industry Standard(s) C/US UL Listed  
Nema Rating Non-NEMA

## Logistics

Carton Quantity 10

## Product Assets

## Related Products

- [RL154 - Lamp Holders and Sockets, Socket Reducer, Mogul to Medium Base, Porcelain](#)
- [RL124H - Lamp Holders and Sockets, Medium Base, 660W 600V AC, Non-Metallic, with Hook](#)
- [RL150 - Lamp Holders and Sockets, Socket Extension, Medium to Medium, Porcelain](#)
- [RL124 - Lamp Holders and Sockets, Medium Base, Pigtail, 660W 250V, Rubber with Leads](#)
- [RL200 - Adapter, Residential Grade, Plug-In, 5- 15R to Medium Base, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RL202-SPEC-EN | REV 7/2023