



Lamp Holders and Sockets, Fluorescent Lamp Holder, Bi-Pin, Pedestal Type, Tall

By Bryant
Catalog # [RL320](#)

Fluorescent Lamp Holder, Bi-Pin, Pedestal Type, Tall



Application

Medium B-Pin, T8 and T12

General

Color	<ul style="list-style-type: none">• White• Blanc
Item Type	Fluorescent Lampholders
Lamp Size	Medium B-Pin, T8 and T12
Material	Composite
Material - Mounting Hardware	Slide On, Snap-In With Captive Nut
Series	Lampholders
Type	Medium Bi-Pin, Fluorescent
UPC	883778112355

Electrical Ratings

Amperage Rating	1.1 A
Connectivity	Screw Terminals
Current / Amperage Rating	1.1 A
Current Rating	1.1 A
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

Certifications and Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant O-3 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RL310 - Lamp Holders and Sockets, Fluorescent Lamp Holder, Slimline, Slide On, Plunger End, Screw Terminals](#)
[RL325B - Lamp Holders and Sockets, Fluorescent Lamp Holder, Bi-Pin, Slide On, 2-Wire, Low Profile](#)
[RL325 - Lamp Holders and Sockets, Fluorescent Lamp Holder, Bi-Pin, Pedestal Type, Low Profile](#)
[RL311 - Lamp Holders and Sockets, Fluorescent Lamp Holder, Slimline, Slide On, Fixed End, Screw Terminals](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL320-SPEC-EN | REV 7/2023