



Lamp Holders and Sockets, Fluorescent Lamp Holder, Bi-Pin, Pedestal Type, Low Profile

By Bryant
Catalog # [RL325](#)



Fluorescent Lamp Holder, Bi-Pin, Pedestal Type, Low Profile

Features

- Fluorescent Lamp Holder
- Bi-Pin
- Pedestal Type
- Low Profile

Application

Medium B-Pin, T8 and T12

General

Catalog Number	RL325
Color	White
EU RoHS Indicator	Yes
Item Type	Fluorescent Lampholders
Lamp Size	Medium B-Pin, T8 and T12
Material	Composite
Material - Mounting Hardware	Slide On, Snap-In With Captive Nut
Series	Lampholders
Specifications	<ul style="list-style-type: none">• Lamp Type - Bi-pin/low profile• Mounting - Slide-on and snap-in with captive nut• Product Type - Medium Bi-Pin Fluorescent

Type	Lampholders
UPC	Medium Bi-Pin, Fluorescent 883778112348

Electrical Ratings

Amperage Rating	1.1 A
Connectivity	Screw Terminals
Current / Amperage Rating	1.1 A
Current Rating	1.1 A
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	28000

Product Assets

[Catalog Page - WDK BB-7](#) [Catalog Page Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - RL325](#)



A Hubbell brand