



Lamp Holders and Sockets, Fluorescent Lamp Holder, Bi-Pin, Slide On, 2-Wire, Low Profile

By Bryant
Catalog # [RL325B](#)

Lamp Holders and Sockets, Fluorescent Lamp Holder, Bi-Pin,
Slide On, 2-Wire, Low Profile



Application

Medium B-Pin, T8 and T12

General

Color	<ul style="list-style-type: none">• White• Blanc
Item Type	Fluorescent Lampholders
Lamp Size	Medium B-Pin, T8 and T12
Material	Composite
Material - Mounting Hardware	Slide On, Snap-In
Series	Lampholders
Type	Medium Bi-Pin, Fluorescent
UPC	883778301841

Electrical Ratings

Amperage Rating	1.1 A
Connectivity	Screw Terminals
Current / Amperage Rating	1.1 A
Current Rating	1.1 A
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

Certifications and Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

Related Products

- [RL311 - Lamp Holders and Sockets, Fluorescent Lamp Holder, Slimline, Slide On, Fixed End, Screw Terminals](#)
- [RL310 - Lamp Holders and Sockets, Fluorescent Lamp Holder, Slimline, Slide On, Plunger End, Screw Terminals](#)
- [RL320 - Lamp Holders and Sockets, Fluorescent Lamp Holder, Bi-Pin, Pedestal Type, Tall](#)
- [RL325 - Lamp Holders and Sockets, Fluorescent Lamp Holder, Bi-Pin, Pedestal Type, Low Profile](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL325B-SPEC-EN | REV 7/2023