



# Fluorescent Lamp Holders, High Output, Slide On, Fixed Side

By Bryant  
Catalog # [RL357](#)

Fluorescent Lamp Holders, High Output, Slide On, Fixed Side



## Application

High Output

## General

Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
Item Type	Fluorescent Lampholders
Lamp Size	High Output
Material	Composite
Material - Mounting Hardware	Slide On, Snap-In
Series	Lampholders
Type	High Output, Fluorescent
UPC	883778303999

## Electrical Ratings

Amperage Rating	1.1 A
Connectivity	Screw Terminals
Current / Amperage Rating	1.1 A
Current Rating	1.1 A
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• C/US UL Listed</li><li>• CSA Certified</li></ul>
----------------------	--

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant O-3 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [RL306 - Lamp Holders and Sockets, Fluorescent Lamp Holder, High Output, Slide On, Fixed End, 2 Terminal Screws](#)
- [RL305 - Lamp Holders and Sockets, Fluorescent Lamp Holder, High Output, Slide On, Plunger End, 2 Terminal Screws](#)
- [RL308 - Lamp Holders and Sockets, Fluorescent Lamp Holder, High Output, Slide On, Plunger End, Low Profile](#)
- [RL356 - Fluorescent Lamp Holders, High Output, Slide On, Plunger Side](#)
- [RL307 - Lamp Holders and Sockets, Fluorescent Lamp Holder, High Output, Slide On, Fixed End, Low Profile](#)



A proud member of the Hubbell Family.