



Lamp Holders and Sockets, Medium Base, Pre-Focus, 1000W 250V, Porcelain

By Bryant
Catalog # [RL3742](#)

Lamp Holders and Sockets, Medium Base, Pre-Focus, 1000W
250V, Porcelain



Application

HID Incandescent

General

Color	<ul style="list-style-type: none">• White• Blanc
Item Type	Replacement Incandescent Lampholders
Lamp Size	Mogul Base
Material	Composite
Material - Mounting Hardware	Screw Mounting
Performance	<ul style="list-style-type: none">• Electrical - Rating - 1500W, 600V Max, 5KV Pulse• Mechanical - Terminal Accommodation - Wire leads: #14 AWG SF-2 (SEW-2) 200° C, 600V glass braid, 12 inch long, stripped 1/2 inch wire
Series	Lampholders
Type	HID Incandescent, Porcelain Keyless
UPC	883778118166

Electrical Ratings

Amperage Rating	4.8 A
Connectivity	Screw Terminals
Current / Amperage Rating	4.8 A
Current Rating	4.8 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

Certifications and Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

Related Products

[RL5221 - Incandescent Lamp Holders, Mogul Base, 5KV, 12" Wire Leads, Screw Mount](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL3742-SPEC-EN | REV 7/2023