



Lamp Holders and Sockets, Mogul Base, 4KV Pulse Start, 12" Leads, Screw Mounted

By Bryant
Catalog # [RL4221](#)



Lamp Holders and Sockets, Mogul Base, 4KV Pulse Start, 12" Leads, Screw Mounted

Application

HID Incandescent

General

Color	White
Item Type	Replacement Incandescent Lampholders
Lamp Size	Mogul Base
Material	Composite
Material - Mounting Hardware	Screw Mounting
Performance	<ul style="list-style-type: none">Electrical - Rating - 1500W, 600V Max, 5KV PulseMechanical - Terminal Accommodation - Wire leads: #14 AWG SF-2 (SEW-2) 200° C, 600V glass braid, 12 inch long, stripped 1/2 inch wire
Series	Lampholders
Type	HID Incandescent, Porcelain Keyless
UPC	883778304033

Electrical Ratings

Amperage Rating	2.5 A
Connectivity	12" Leads
Current / Amperage Rating	2.5 A
Current Rating	2.5 A
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RL4221-SPEC-EN | REV 7/2023