



Fluorescent Lamp Holders, Compact Type, 18-55 Watt 2G11, 90 Degree Horizontal Mount, Snap-In

By Bryant
Catalog # [RL42G11H9](#)



Fluorescent Lamp Holders, Compact Type, 18-55 Watt 2G11, 90
Degree Horizontal Mount, Snap-In

General

Application	Compact Fluorescent
Catalog Number	RL42G11H9
Color	White
EU RoHS Indicator	No
Item Type	Fluorescent Lampholders
Lamp Size	2-G11 Base 4) Pin
Material	Composite
Material - Mounting Hardware	Vertical Snap-In
Performance	Electrical - Rating - 26-32W lamp type, 75W, 600V Mechanical - Terminal Accommodation - Push-in wire terminals for #18 AWG solid or twist and tin stripped 7/16 inch wire
Series	Lampholders
Type	Compact Fluorescent
UPC	883778303951

Electrical Ratings

Connectivity	Screw Terminals
Current Rating	Telephone/CATV
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

Certifications And Compliance

Industry Standard(s)	C/US UL Listed CSA Certified
----------------------	---------------------------------

Logistics

Carton Quantity	10
Pallet Quantity	2000

Product Assets

- [Catalog Page - WDK BB-7 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand